

Material number	0 611 911 000	0 611 911 001	0 611 911 073
EAN	3165140860208	3165140860185	3165140867603
2 x battery GBA 18V 5.0 Ah 1 600 A00 2U5			✓
AL 1860 quick charger 2 607 225 323			✓
Carrying case			✓
Carton 6 082 765 72B	✓		
Depth stop		✓	
L-BOXX 136		✓	
Machine cloth		✓	

## Technical data

### Technical data

Max. impact energy	1.7 J
Impact rate at rated speed	0 – 4.550 bpm
Rated speed	0 – 1.800 rpm
Battery voltage	18 V

### Drilling range

Drilling dia. in concrete with hammer drill bits	4 – 20 mm
Max. drilling diameter in steel	13 mm
Max. drilling diameter in wood	30 mm



## Sales information

### Positioning

- Cordless hammer as powerful as corded now made affordable

### User benefit

- Bosch quality at an affordable price
- High performance: as fast as corded. Same impact energy, same drilling capacity and same speed as GBH 2-20
- Interchangeable carbon brush gives high serviceability