

Metric Nylon Cable Gland

pro-POWER


RoHS
Compliant



Features

- High grade nylon cable glands
- Available in black
- IP65 rating
- Low smoke
- Halogen free
- Lock nut included
- Sealing: Ding qing rubber
- CE compliant

Diagram



Dimension Table

Part Number	Size (mm)	GL (mm)	H (mm)
M12DB	3 to 6.5	8	22
M16DB	4 to 8	8	26
M20DB	6 to 12	9	28
M25DB	13 to 18	10	35
M32DB	14 to 21	11	34

Part Number Table

Description	Pack Quantity	Part Number
M12 Nylon Cable Gland Black	10 pcs	M12DB
M16 Nylon Cable Gland Black		M16DB
M20 Nylon Cable Gland Black		M20DB
M25 Nylon Cable Gland Black		M25DB
M32 Nylon Cable Gland Black		M32DB

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com
www.farnell.com
www.newark.com
www.cpc.co.uk

pro-POWER