



Pushbutton switches

9052.0200

Product number	9052.0200	
Business unit	Switches, Sensors & Controls	
Product family	Pushbutton switches	
Actuation type	direct	
Packing unit		100
Output	catalogue miniature switch	
Switching function	Changeover switch (DPDT momentary)	
Material fixed contact	Ag	
Contact system	Electrical life	25000
Number of poles	2 - pole	
connections	Solder terminal, sealed	
Mechanical life endurance		100000
Rating IEC	4 A 30 V DC	
	5 A 48 V AC	
Contact resistance (new condition)	< 20 mOhm	
Insulation resistance (new condition)	> 1000 MOhm	
Voltage strength at 250 V	small contact distance	> 1000 V
Ambient temperature	-25 °C ... +70 °C	
Actuators and additional actuators	actuator: CurZn nickel-plated	
Housing description	threaded socket: CnZn nickel-plated, hexagonal nuts of nickel-plated CuZn	
	bracket plate: stainless steel	
	base plate: DAP, olivegreen	
Connection surface	bearing connection	silver plated
	external connection	silver plated
Contact material	Ag	
Contact type	lifting contact	
Operating force	10 N	
Miscellaneous	corresponding pushbuttons 9090.03.. see additional parts / stroke 1.8 mm	
Type of fastening	central fastening M6 x 0.75	

Technical changes reserved. Dimensions are not binding.

Detailed specifications available on request.