

PNOZ m ES Profibus

772132



Configurable control system PNOZmulti 2 expansion module
Communication module PROFIBUS.

Technical details

Approvals:	CE;cULus Listed;CCC
Fieldbus interface:	PROFIBUS-DP
Fieldbus connection:	Female 9-pin D-Sub connector
Fieldbus type:	Slave DPV0
Number of PROFIBUS-DP interfaces:	1
Version for extreme environ. conditions:	Standard
Width dimension:	22.5 mm
Height dimension:	101.4 mm
Depth dimension:	115.0 mm
Gross weight:	105 g
Net weight:	95 g
Ambient temperature:	0 - 60 °C

Accessories



783542

Spring terminals PNOZ mmcxp, 1 pc.



793542

Screw terminals PNOZ mmcxp, 1 pc.

Optional accessories



779260

PNOZ mm0.xp connector left (10 pcs)



793543

Screw terminals PNOZ mmcxp, 10 pcs.



783543

Spring terminals PNOZ mmcxp, 10 pcs.