

## PNOZ m ES EtherCAT

772136



Configurable control system PNOZmulti 2 expansion module  
Communication interface EtherCAT.

### Technical details

Approvals:	CE;cULus Listed;CCC
Fieldbus interface:	EtherCAT
Fieldbus connection:	RJ45
Fieldbus type:	Slave
Transmission rate:	100 MBit/s
Version for extreme environ. conditions:	Standard
Width dimension:	22.5 mm
Height dimension:	101.4 mm
Depth dimension:	115.0 mm
Gross weight:	95 g
Net weight:	85 g
Ambient temperature:	0 - 60 °C

### Accessories



783542

Spring terminals PNOZ mmcxp, 1 pc.



793542

Screw terminals PNOZ mmcxp, 1 pc.

## Optional accessories



779260

PNOZ mm0.xp connector left (10 pcs)



793543

Screw terminals PNOZ mmcxp, 10 pcs.



783543

Spring terminals PNOZ mmcxp, 10 pcs.