

Products → Low Voltage Products and Systems → Enclosed Switches → Enclosed Cam Switches

General Information

Extended Product Type:	ONA3EKB
Product ID:	1SCA022662R3760
EAN:	4034656524067
Catalog Description:	ONA3EKB Enclosed cam switch
Long Description:	Key type, protection class IP54

Additional Information

Ampere Rating UL/CSA:	600 V AC 25 A
Cable Entry Position:	Up/Down
Cable Outlets Per Side:	M knock-outs
Color:	Black
Conventional Free-air Thermal Current (I_{th}):	q = 40 °C 25 A
Country of Origin:	Germany (DE)
Customs Tariff Number:	85365080
Data Sheet, Technical Information:	1SCC302003C0201
Declaration of Conformity - CE:	1SCC302001D0204
Degree of Protection:	IP54
E-number:	3146278
EAN:	4034656524067
ETIM 5:	EC002611 - Control switch
ETIM 6:	EC002611 - Control switch
Enclosure Material:	Plastic
Enclosure Type:	Enclosed
Environmental Information:	1SCC302003D0201
Function:	A3
Handle Type:	Key operated
IIT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SCC302004M0203
Invoice Description:	ONA3EKB Enclosed cam switch
Minimum Order Quantity:	1 piece
Mounting Type:	Switch in enclosure
Number of Contacts:	3
Number of Poles:	3
Object Classification Code:	Q
Package Level 1 EAN:	4034656524067
Package Level 1 Gross Weight:	0.3 kg
Package Level 1 Height:	100 mm
Package Level 1 Length:	96 mm
Package Level 1 Units:	1 piece
Package Level 1 Width:	96 mm
Pollution Degree:	3
Price Category:	Standard
Product Main Type:	ON

Product Name:	Cam switch
Product Net Depth:	70 mm
Product Net Height:	96 mm
Product Net Weight:	0.3 kg
Product Net Width:	96 mm
Rated Continuous Thermal Current:	FullyEnclosed 25 A
Rated Impulse Withstand Voltage (U_{imp}):	4 kV
Rated Insulation Voltage (U_i):	690 V
Rated Operational Current AC-22A (I_e):	(500 V) 20 A (690 V) 20 A
Rated Operational Power AC-23A (P_e):	(220 ... 240 V) 2.6 kW (415 V) 7.5 kW (500 V) 4.8 kW (690 V) 4.8 kW
Rated Operational Voltage:	400 V
RoHS Information:	1SCC302004D0201
Selling Unit of Measure:	piece
Short Description:	Enclosed
Special Functions:	ON - OFF switch: 0-position: 9 o'clock, key operated, step angle 90°, front plate 0-1
Terminal Type:	Screw Terminals

