

Share:



SYBT2

Average Customer Review ★★★★★ 5

1 of 1 (100%) reviewers would recommend this product to a friend.

[Read all reviews](#) | [Write a review](#)

Share this Product: [f](#) [G+](#) [T](#) [P](#)



Product Overview **Technical Specifications** Documentation Ratings & Reviews

Input		Print Technical Specification
Number of Power Cords	1	
Batteries & Runtime		
Battery type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof	
Battery mounting	Enclosed battery cartridge	
Battery Placement	Internal Battery	
Expected Battery Life (years)	3 - 5	
RBC Quantity	1	
Physical		
Maximum Height	3.25inches (83mm , 8.3CM)	
Maximum Width	8.5inches (216mm , 21.6CM)	
Maximum Depth	21.5inches (546mm , 54.6CM)	
Rack Height	2U	
Net Weight	49.0lbs. (22.27KG)	
Shipping weight	52.5lbs. (23.86KG)	
Shipping Height	9.75inches (248mm , 24.8CM)	
Shipping Width	14.0inches (356mm , 35.6CM)	
Shipping Depth	26.0inches (660mm , 66.0CM)	
Color	Beige	
Units per Pallet	12.0	
Environmental		
Operating Temperature	32 - 104 °F (0 - 40 °C)	
Operating Relative Humidity	0 - 95 %	
Operating Elevation	0-10000ft (0-3000meters)	
Storage Temperature	-15 - 45 °C	
Storage Relative Humidity	0 - 95 %	
Storage Elevation	0-50000ft (0-15000meters)	
Conformance		
Standard warranty	2 years repair or replace, optional on-site warranties available, optional extended warranties available	
Sustainable Offer Status		
RoHS	Compliant	
REACH	REACH: Contains No SVHCs	
PEP	Available in Documentation tab	
EOLI	Available in Documentation tab	
Other Environmental Compliance	China RoHS	



Careers
Sustainability

Schneider Electric TV
Schneider Electric Data Center Blog
Contact Us
Rate this website

[TERMS & CONDITIONS](#) | [PRIVACY STATEMENT](#)

© 2018, APC by Schneider Electric

