

Steel Digital Caliper


D03196

0-15mm/ 0-16" Digital Caliper


FEATURES

High precision digital readout on clear LCD display
 Robust stainless steel construction
 Locks jaws in place with locking screw
 Thumbwheel for precise and smooth adjustment
 Imperial or metric units at the touch of a button

Depth measuring blade
 Step-measuring faces
 For internal and external measurements
 Low battery level indicator



MEASUREMENTS



SPECIFICATIONS

Range	0~150mm/ 6"
Resolution	0.01mm/0.0005"
Repeatability	0.1mm/ 0.01"
Power	One 1.5 V cell battery <input type="checkbox"/>
	One CR2032 3 V battery <input checked="" type="checkbox"/>
Influence of humidity	Up to 80% non-condensing
Operating temperature	0 °C~40 °C
Storage temperature	-20°C~60°C

BATTERY REPLACEMENT

