

Product information

18V Router/Trimmer BL LXT



DRT50ZJ

Battery Type	Lithium-ion
Body only machine	1
Voltage	18 v
Collet Capacity	3/8" and 1/4"
Noise sound pressure	78 dB(A)
Noise K factor	3 dB(A)
Plunge Capacity (Trimmer)	0 - 40 mm
Plunge Capacity (Plunge)	0 - 35 mm
No Load Speed	10,000 - 30,000 rpm
Vibration K factor	1.5 m/sec ²
Vibration: Cutting MDF	4.5 m/sec ²
Vibration no load	2.5 m/sec ²
Net weight	2.1 kg



LITHIUM-ION

BL
MOTOR

STANDARD EQUIPMENT: 821552-6 MAKPAC CONNECTOR CASE (TYPE 4), Trimmer base, Straight guide, Dust nozzle for trimmer base, Hex wrench x2, Collet cone, Template guide for trimmer

- Brushless motor
- Soft start
- Variable speed control dial.
- Constant speed control
- LED job light
- Push button with lock on/off
- Connectable to dust extractor
- Aluminium base for higher durability and accuracy
- Aluminium housing
- Shaft lock

Details correct as of: 9-1-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com