

# Product information

## 10.8V Multi Cutter CXT



Satisfying the professional's needs

### CP100DZ

Battery Type	Lithium-ion
Body only machine	1
Voltage	10.8 v
Cutting Capacity	6 mm
Noise sound pressure	70 dB(A)
Noise K factor	3 dB(A)
No Load Speed	300 rpm
Vibration K factor	1.5 m/sec <sup>2</sup>
Vibration no load	2.5 m/sec <sup>2</sup>
Net weight	0.88 kg



- Compact size for excellent manoeuvrability
- Ergonomic soft grip
- Lock-off button for safe operation
- Auto self-sharpening function: maintains sharp performance by automatically sharpening blade every time the blade rotates
- Suitable for cutting a range of materials including: cardboard, carpet, vinyl and lino flooring, artificial grass, roofing felt, fibre-glass rendering mesh, damp-proof course, weed control membrane, tarpaulin, pallet strapping, wire mesh and more.

Details correct as of: 9-1-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

[www.makita.com](http://www.makita.com)