

Product information

18Vx2 Plunge Saw 165mm BL LXT



Satisfying the professional's needs

DSP600ZJ

Max Cut @ 48°	38 mm
Battery Type	Lithium-ion
Body only machine	1
Voltage	36 (18V x2) v
Blade Diameter	165 mm
Max Cut @ 0°	56 mm
Max Cut @ 45°	40 mm
Bore (B)	20 mm
Noise sound pressure	92 dB(A)
Noise sound power	103 dB(A)
Noise K factor	3 dB(A)
No Load Speed	2,500 - 6,300 rpm
Vibration K factor	1.5 m/sec ²
Vibration: Cutting Wood	2.5 m/sec ²
Net weight	5.1 kg



BL MOTOR **LITHIUM-ION**

STANDARD EQUIPMENT: 821552-6 MAKPAC CONNECTOR CASE (TYPE 4), TCT saw blade, Hex wrench

- Electric brake
- Variable speed control dial.
- Soft start
- Automatic Torque Drive Technology: Automatically changes the cutting speed according to load condition for an optimum operation
- Brushless motor
- Depth stopper for splinter free cutting
- Bevels -1 to 48 degrees
- Positive stop for bevel adjustment
- Powered by two 18V Li-ion batteries in series to supply energy to the powerful 36V DC motor drive system.
- Compatible with Guide Rail

Details correct as of: 11-1-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com