



Sample photo

Order symbol: PCQ3 153410
Product nbr: 7035701
Description: Enclosure, PC
Remarks: Grey cover (quick-locking)

EAN: 6418074099136
EI. number:
Finland: 3424198

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and quick-locking cover screws.

Dimensions:				Accessories:		
Length	Width	Height				
mm:	340	150	101	TRH 34	DIN-35 Mounting rail	
inch:	13.4	5.9	4.0	TRH 15	DIN-35 Mounting rail	
Materials:				TF 28037	Wall fastening lug (4 pcs)	
Material:	Polycarbonate		TH A	Grey plastic hinges (2 pcs)		
Base colour:	RAL 7035 -light grey		EU 3 QuickLock set 60	QuickLock screws (60 pcs)		
Cover screws material:	Stainless steel		MR 28036EU Set 60	Mounting screws (60 pcs)		
Cover colour:	RAL 7035 -light grey		EU 3 Plug set 60/30	EU 3 Cover screw plug set 60/30		
Gasket material:	Polyurethane		EU 3 Plug set 60/30 BL	EU 3 Cover screw plug set 60/30 black		
Temperatures:				Rating:		
Temperature °C (short term):	-40 ... 120 °C		Ingress Protection (EN 60529): IP66/IP67			
Temperature °C (continuous):	-40 ... 80 °C		Impact Resistance (EN 62262): IK07/IK08			
Temperature °F (short term):	-40 ... 250 °F		Electrical insulation: Totally insulated			
Temperature °F (continuous):	-40 ... 175 °F		Halogen free (DIN/VDE 0472, Part 815): 1			
Accessories:				Glow Wire Test (IEC 695-2-1) °C: 960		
TM 1534	Mounting plate		Certificates:			
			SGS Fimko			
			Gost R			

