

Thin Client Mount - VESA Mounting Bracket

Product ID: ACCSMNT



This thin-client mounting bracket provides an excellent space-saving solution, by letting you mount your thin-client PC or docking station to create a clutter-free workspace.

Multiple installation methods

The versatile double-sided VESA mount offers several installation options, enabling you to mount your thin-client PC or dock to the back of your monitor or under your desktop, or clamp it to a monitor-mount pole. The mount supports 75x75, and 100x100 VESA mount compatibility, making it suitable for most monitors and monitor mounts.

Store a variety of products

This adjustable mount is ideal for holding an Intel® NUC, Mac Mini, most small CPUs, thin clients, docking stations, or USB hubs that fit within the width adjustability of the mount (.7" to 2.8" / 17 mm to 70 mm). The mount can support up to 11 lb. (5 kg). It also features an adjustable strap to help keep your devices secure, and rubber pads to secure products with non-parallel surfaces.

Unrestricted Access

The open-frame design of the mount allows unrestricted access to your computer.

The ACCSMNT is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Create a clutter-free work space in office, business, commercial and institutional environments
- Enhance your home office by maximizing your desktop space

Features

- Save space and reduce cable clutter by mounting your thin-client PC or docking station to the back of your monitor, clamped to a monitor-mount pole, or under your desk
- Supports up to 11 lb. (5 kg)
- Adjustable width from .7" to 2.8" (17 mm to 70 mm)
- 75x75 and 100x100 VESA mount compatibility
- Rubber pads to prevent damage to your device
- Keep your device secure with the adjustable strap
- Easily access your computer with the open-frame design

Hardware	Warranty	5 Years
	Mounting Options	Back of Monitor, Under Desktop, or Clamped to Monitor-Mount Pole
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
Special Notes / Requirements	Note	The adjustable mount is designed for holding small CPUs, thin clients, docking stations, or USB hubs that fit within the width adjustability of the mount: .7" to 2.8" (17 mm to 70 mm).
Physical Characteristics	Color	Black
	Enclosure Type	Steel and Plastic
	Product Height	95 mm [3.7 in]
	Product Length	118 mm [4.6 in]
	Product Weight	666 g [23.5 oz]
	Product Width	80 mm [3.1 in]
Packaging Information	Shipping (Package) Weight	776 g [27.4 oz]
What's in the Box	Included in Package	1 - mounting bracket
		1 - adjustable strap
		1 - pole mount
		6 - pads
		2 - M5x25 mm screws
		8 - M4x12 mm screws
		4 - M4 nuts
		4 - screws
		4 - washers
		1 - instruction manual

Product appearance and specifications are subject to change without notice.