

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301040026](#)  
**Status:** **Active**  
**Overview:** [Specialty Lighting](#)  
**Description:** Haztex Hazardous Location 26W with 12V Fluorescent Hand Lamp with In-line Transformer 16/3 SOOW Cord Type, Cord Length 15.24m (50.0')

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

**Agency Certification**

CSA	LR39801
UL	E30252

**General**

Product Family	Portable Lighting
Series	<a href="#">130104</a>
Comments	Class I, Division 1, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone 1, Group IIB (UL)
NEMA Configuration	NEMA 5-15
Outlet	None
Overview	<a href="#">Specialty Lighting</a>
Product Literature Order No	987650-8052
Product Name	Haztex
Type	Hand Lamps, Specialty Light
UPC	78678805478
Woodhead	Yes

**Physical**

Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Depth	100.08mm (3.940")
Duty	Hazardous
Guard Included	No
Guard Type	N/A
Height	482.60mm (19.000")
Length	N/A
Material - Globe	Tempered Soda-Lime Glass
Material - Guard	Cast Aluminum
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A

**Electrical**

Bulb Type	Fluorescent
Cord Type - Primary	16/3 SOOW
Lamp Type	PL-C 26/41/4P
Lamp Wattage - Maximum	26W
Lumens	1800
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Voltage (Secondary) - Maximum	12V AC

**Material Info**

Engineering Number	1090-HZ12IB163
--------------------	----------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

130104 Series

This document was generated on 10/11/2017

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**