

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301090007](#)  
**Status:** **Active**  
**Overview:** [Hand Lamps](#)  
**Description:** Safeway Nylon 100W Hand Lamp with Molded, 16/3 SJTOW Cord Type, Metal Guard, Overall Cord Length 7.62m (25.0')

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

**Agency Certification**

CSA LR85437  
 UL E59049

**General**

Product Family Portable Lighting  
 Series [130109](#)  
 NEMA Configuration NEMA 5-15  
 Outlet None  
 Overview [Hand Lamps](#)  
 Product Literature Order No 987650-8053  
 Product Name Safeway  
 Type Hand Lamps  
 UPC 78678861601  
 Woodhead Yes

**Physical**

Cord Length - Primary 7.62m (25.0')  
 Cord Length - Secondary N/A  
 Depth N/A  
 Duty General  
 Guard Included No  
 Guard Type N/A  
 Height N/A  
 Length N/A  
 Material - Guard #8 Gauge Zinc-plated Steel  
 Mounting Style Hand Held  
 Packaging Type Carton  
 Socket Construction N/A

**Electrical**

Bulb Type Incandescent  
 Cord Type - Primary 16/3 SJTOW  
 Lamp Type A21  
 Lamp Wattage - Maximum 100W  
 Lumens 1000  
 On/Off Switch Yes  
 Voltage (Fixture) - Maximum 120VAC 60 HZ

**Material Info**

Engineering Number 402



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Not Reviewed

ELV Not Reviewed

RoHS Phthalates Not Reviewed

**Search Parts in this Series**

[130109](#) Series