

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300980155](#)
Status: **Active**
Overview: Strain-Relief Cord Grips
Description: MAX-LOC Strain Relief Cord-Sealing Grip, 1" NPT, Straight Male, Cable Diameter 19.05-22.23mm (.750-.875")

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

Agency Certification

CSA LR32159
UL E76954

General

Product Family Cable Grips
Series [130098](#)
Eye Type N/A
NEMA Rating NEMA 3R
O-Ring No
Overview [Strain-Relief Cord Grips](#)
Product Literature Order No 987651-6081
Product Name MAX-LOC
Type Strain Relief Grip
UPC 78678872133
Use With MAX-LOC Lock Nut 1" NPT [130099-0145](#) , MAX-LOC Gasket Sealing Ring 1" NPT [130099-0151](#) , MAX-LOC O-Ring, 1" NPT [130180-0334](#)

Woodhead Yes

Physical

Approximate Break Strength N/A
Bale Length N/A
Body Style Straight
Cable Diameter 19.05-22.23mm (.750-.875")
Color - Grommet N/A
Gender Male
Material - Body Nylon
Material - Grip N/A
Mesh Length N/A
Number of Holes 1
Thread Size 1" NPT

Material Info

Engineering Number 5556



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[130098](#) Series