

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300970165](#)  
**Status:** **Active**  
**Overview:** [Strain-Relief Cord Grips](#)  
**Description:** Deluxe Cord Grips Strain Relief, 1/2" NPT, Straight Male, Cable Diameter 12.70-15.88mm (.500-.625")

**Documents:**

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR32159  
 UL E76954

**General**

Product Family Cable Grips  
 Series [130097](#)  
 Eye Type N/A  
 Hazardous Locations Class I, Div. 2, Class II, Div. 1 and 2, Class III, Div. 1 and 2  
 NEMA Rating NEMA 4  
 O-Ring N/A  
 Overview [Strain-Relief Cord Grips](#)  
 Product Literature Order No 987651-6081  
 Product Name Deluxe Cord  
 Type Strain Relief Grip  
 UPC 78678836256  
 Use With 1/2" NPT MAX-LOC Lock Nut [130099-0143](#) , MAX-LOC O-Ring, 1/2" NPT [130180-0314](#) , 1/2" NPT MAX-LOC Gasket [130099-0149](#)  
 Woodhead Yes

**Physical**

Approximate Break Strength N/A  
 Bale Length 0.089m (3.50")  
 Body Style Straight  
 Cable Diameter 12.70-15.88mm (.500-.625")  
 Color - Grommet N/A  
 Gender Male  
 Material - Body Aluminum  
 Material - Grip Stainless Steel  
 Mesh Length 0.178m (7.00")  
 Number of Holes N/A  
 Thread Size 1/2" NPT

**Material Info**

Engineering Number 36256

**Reference - Drawing Numbers**

Sales Drawing SD-130097-103



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[130097](#) Series