

**Model#: 29-9500**



**Product Specifications**

Built-in Battery	12000mAh,3.7V,44.4Wh High Rate Discharge Lithium Polymer Batteries
Input charging	DC15V/1A
Fully Charged Time	DC 15V/1A:4~5 hours
Charge mode	CC/CV
Jumpstart Output	EC5; Support 12V Battery System Vehicle
Output	Dual USB outputs,5V/3.1A Max
DC Wattage(MAX)	-
Bulb Type	Ultra bright LED light/SOS
Power Indicator	4 Indicators
Peak Current	650A
Operation temperature	-10°C-60°C
Lifecycle	500 times
MultiSafety Protection 2.0	a.Delay protection b.Short-circuit protection c.Reverse polarity protection d.Over-current protection e.Over-voltage protection f.Low-voltage protection g.Reverse filling protection h.Overfrequency protection i.Over-temperature protection

**Package include**

- 1 x Tool bag
- 1 x car jump starter
- 1 x Smart clamps T103
- 1 x power adapter
- 1 x MicroUSB charging cable
- 1 x car charger
- 1 x user manual

**Benefits**

**Selling points:**  
**Peak Current up to 650A**  
1.Built in 12000mAh /3.7V High Rate Discharge Lithium Polymer Batteries  
2.Jumpstart 12V Gasline car up to 6.0L  
3.Dual USB outputs for mobile phones  
4.Ultra bright torch/blink/SOS  
5.Weight 460g, Light Weight to carry  
6.Equipped with SmartClamps T103.  
7.Mistake proof including: Shortcircuit, Reverse polarities proof etc.,