

W WELDY

pic pro plus

ergonomic and multi-functional hot air tools.



WELDY plus

simple. good. affordable.

WELDY hot air tools

Article numbers

119.364	100 V / 1100 W	US plug non pol. (J)
119.380	120 V / 1200 W	US plug polarized
119.475	230 V / 1600 W	CN plug
119.055	230 V / 1600 W	EU plug
119.076	230 V / 1600 W	CH plug
119.084	230 V / 1600 W	UK plug
119.225	230 V / 1600 W	AUS plug

pic



- Air flow adjustment with a two-step switch

pic

Article numbers

119.365	100 V / 1200 W	US plug, non pol. (J)
119.381	120 V / 1400 W	US plug, polarized
119.476	230 V / 1800 W	CN plug
119.056	230 V / 1800 W	EU plug
119.077	230 V / 1800 W	CH plug
119.085	230 V / 1800 W	UK plug
119.226	230 V / 1800 W	AUS plug

pro



- Temperature adjustment with potentiometer
- Air flow adjustment with a two-step switch

pro

Article numbers

119.366	100 V / 1300 W	US plug non pol. (J)
119.995	120 V / 1500 W	UK plug (110 V / 16 A)
119.477	230 V / 2000 W	CN plug
119.057	230 V / 2000 W	EU plug
119.078	230 V / 2000 W	CH plug
119.086	230 V / 2000 W	UK plug
119.227	230 V / 2000 W	AUS plug
119.442	230 V / 1600 W	without plug

plus



- Electronical temperature and air-flow adjustment
- 14 preset programs for plastic welding
- LCD display
- Stand-by for eco drive
- Heating element protection
- Multilingual menu (D, ES, FR, GB, IT, NL, PT, SE)
- Wide range of accessories

plus

pic



WELDY hot air tool kits

Article numbers

122.707	100 V / 1100 W	US plug (J)
122.703	120 V / 1200 W	US plug (UL)
119.896	230 V / 1600 W	CN plug
122.561	230 V / 1600 W	EU plug
122.563	230 V / 1600 W	CH plug
122.565	230 V / 1600 W	UK plug
122.746	230 V / 1600 W	AUS plug (2 P + PE)

pic

pro



Article numbers

122.716	100 V / 1200 W	US plug (J)
122.719	120 V / 1400 W	US plug (UL)
119.897	230 V / 1800 W	CN plug
119.274	230 V / 1800 W	EU plug
122.614	230 V / 1800 W	CH plug
122.554	230 V / 1800 W	UK plug
122.753	230 V / 1800 W	AUS plug (2 P + PE)

pro

plus




Article numbers

122.841	100 V / 1300 W	US plug non pol. (J)
119.382	120 V / 1500 W	US plug polarized
122.843	120 V / 1500 W	US plug pol. (UL)
122.849	120 V / 1500 W	UK plug
119.898	230 V / 2000 W	CN plug
122.324	230 V / 2000 W	EU plug
122.845	230 V / 2000 W	CH plug
122.847	230 V / 2000 W	UK plug
122.852	230 V / 2000 W	AUS plug

plus

Accessories

		Article no.	pic	pro	plus
1	Glass protection nozzle	119.341	○	●	○
2	Wide slot nozzle	119.342	●	–	○
3	Reducer nozzle Ø 20 mm	119.343	○	●	○
4	Reflector nozzle	119.344	●	●	●
5	Welding nozzle	119.345	–	–	●
6	Overlap welding nozzle	119.346	–	–	●
7	Solder sleeve reflector	119.347	–	–	●
8	Pressure roller	119.348	–	–	●
	Robust storage case		●	●	●
● Included in the kit			○ Not included in the kit		– Not applicable



Glass protection nozzle



Wide slot nozzle



Reducer nozzle Ø 20 mm



Reflector nozzle



Welding nozzle



Overlap welding nozzle



Solder sleeve reflector



Pressure roller

pic pro plus

Technical data

		pic	pro	plus
Voltage	V	230	230	230
Power consumption	W	1600	1800	2000
Temperature range	°C	350 / 500	100 – 550	80 – 650
Air flow	l/min.	350 / 500	250 / 550	200 – 550 (continuously variable)
Static pressure max.	Pa	1400	1500	1500
Weight with cord	g	680	720	780

Applications



pendulum welding
• pic • plus



forming
• pic • pro • plus



soldering of copper tubes
• pro • plus



shrinking
• pic • pro • plus



edge banding
• plus



shrinking of tubes
• plus



loosening of screws
• pic • pro • plus



paint stripping
• plus



remove of stickers and films
• pic • pro • plus



Further WELDY tools



energy 1600 / energy 3400

- For professional use
- 1600 / 3400 W power
- Construction site approved
- Handy and reliable



foiler / foiler ET

- Hot air welder for tarps and banners
- Welding speed up to 7.5 m/min.
- Easy handling

Your distributor

WELDY
Galileo-Strasse 10

CH-6056 Kaegiswil
Switzerland

Australia info@weldy.com.au www.weldy.com.au
New Zealand info@weldy.co.nz www.weldy.co.nz