


### DESTB-0403

3 Pole steatite ceramic high temperature blocks terminal 41a 750v



### SPECIFICATION

<b>Number of Poles</b>	3
<b>Body Material</b>	Steatite
<b>Colour</b>	White
<b>Min Conductor Size (Sq mm)</b>	1.5
<b>Max Conductor Size (Sq mm)</b>	10
<b>Min Conductor Size AWG</b>	22
<b>Max Conductor Size AWG</b>	10
<b>Max Current (A)</b>	41
<b>Max Voltage (V)</b>	750
<b>Minimum Temp Rating °C</b>	-40
<b>Max Temp Rating °C</b>	300-350
<b>Pitch (mm)</b>	14
<b>Height (mm)</b>	21
<b>Width (mm)</b>	22
<b>Length (mm)</b>	38
<b>Comments</b>	M3.5 conductor clamping screws, maximum torque=0.8Nm