

# PRODUCT SPECIFICATION

EN#: 4710810406676

## SD-2314M 25 In 1 Reversible Ratchet Screwdriver W/Bits & Sockets Set



### Safety and environmental protection:

- RoHS & Pb free: RoHS

### Handle:


- Material of handle: PP, TPR
- Handle O.D. (mm): 31.5

### Blade:

- Color of blade: Primary colors, Black
- Blade hardening: Quench hardening process
- Shape of blade: Round head

### Bits:

- 單顆套筒\_規格內容


The first type symbol	六角孔電鍍	Socket Length (mm)	材質打印	規格打印	PK LOGO打印	Quick way binding site
 Nut	shine-sided	25	Yes	Yes	Non	Non

 Nut	shine-sided	25	Yes	Yes	Non	Non
 Nut	shine-sided	25	Yes	Yes	Non	Non
 Nut	shine-sided	25	Yes	Yes	Non	Non
 Nut	shine-sided	25	Yes	Yes	Non	Non
 Nut	shine-sided	25	Yes	Yes	Non	Non
 Nut	shine-sided	25	Yes	Yes	Non	Non

• 延長桿\_規格內容

The first type symbol	鐵桿外徑 D2 (mm)	本體電鍍	全長 L (mm)	材質打印	PK LOGO打印	球型雙用設計	快拆裝置	滾珠裝置	Joints binding mode
 Square	10	shine-sided	60	Non	Non	Non	Non	Non	Non

• 棘輪手柄\_規格內容





The first type symbol	Surface Finish	Specifications Print	Material Print	PK LOGO	Angle and teeth	Ratchet direction switch	Joints binding mode
 Nut	Satin finish	Non	Non	Yes	Non	Non	Non

• Torx

The first type symbol	Head Specifications	六角對邊尺寸	Surface Finish	Bit Length (mm)	Color	規格打印	材質打印
 Torx	T15	6.35mm (1/4")	Sand blasting	25	Non	Yes	Yes
 Torx	T20	6.35mm (1/4")	Sand blasting	25	Non	Yes	Yes

• specification contents

The first type symbol	Head Specifications	六角對邊尺寸	Surface Finish	Bit Length (mm)	本體色環	規格打印	材質打印
 Slotted	SL3.0mm	6.35mm (1/4")	Sand blasting	25	Non	Yes	Yes
 Slotted	SL4.0mm	6.35mm (1/4")	Sand blasting	25	Non	Yes	Yes
 Slotted	SL5.0mm	6.35mm (1/4")	Sand blasting	25	Non	Yes	Yes
 Slotted	SL6.0mm	6.35mm (1/4")	Sand blasting	25	Non	Yes	Yes
 Slotted	SL7.0mm	6.35mm (1/4")	Sand blasting	25	Non	Yes	Yes
 Slotted	SL7.0mm	6.35mm (1/4")	Sand blasting	110	Non	Yes	Non
 Phillips	PH0	6.35mm (1/4")	Sand blasting	25	Non	Yes	Yes
 Phillips	PH1	6.35mm (1/4")	Sand blasting	25	Non	Yes	Yes
 Phillips	PH2	6.35mm (1/4")	Sand blasting	25	Non	Yes	Yes

 Phillips	PH3	6.35mm (1/4")	Sand blasting	25	Non	Yes	Yes
 Phillips	PH2	6.35mm (1/4")	Sand blasting	65	Non	Yes	Non
 Phillips	PH2	6.35mm (1/4")	Sand blasting	65	Non	Yes	Non
 Phillips	PH2	6.35mm (1/4")	Sand blasting	150	Non	Yes	Non

**Product Weight (w/o package):**

Weight(g)	Measurement		
744.8	L(mm)	W(mm)	H(mm)
	223	183	37

**Individual Packing**

- Packing: Shink Parking

**Master Packing:**

	Pieces	N.W. (Kg)	G.W. (Kg)	Measurement			CUFT
				L(cm)	W(cm)	H(cm)	
Individual Packing	1	-	0.75	22.3	18.3	3.7	-
Inner Box	6	4.5	4.71	24	20	21	0.36
CTN	24	18.4	19.4	49	42	23.5	1.71