

# 6228-0001- Footswitch 2822791

- Low profile, rear hinged switch designed for improved user comfort
- All plastic construction with raised tread pattern
- Yellow cover with black base fitted with M3 inserts & neoprene pad
- Complete with 2 meters of 3 core cable free wire ends
- Single pole change over / Silver contacts
- Momentary action
- Sealed to IPX7
- Electrical rating: 3A 250V AC
- Operating Temperature: -20°C to +60°C



## Reference dimensions

