

SylCircle

SYLCIRCLE 6W 410LM 4000K

0043260



Range Features

- Ceiling / wall luminaire with integrated LED
- Perfect solution for hallways, kitchens or applicable zone 2 bathroom and wet areas thanks to its IP44 rating
- Even and uniform light distribution with a halo lighting effect on the wall surface
- 6W
- 410 lumens
- Supplied with LED driver (non-dimmable)
- IK03 PMMA diffuser
- Low maintenance with 30,000 hours LED life expectancy



PRODUCT OVERVIEW

Certifications	CE
Colour temperature (K)	4000
Colour	White
CRI (Ra)	80
Dimmable	Non-dim / not dimmable (switched only)
EAN code	5410288432601
Luminous flux (lm)	410
Housing	Aluminium
IK rating	IK03
IP rating	IP44
Light colour	Neutral white
LOR (%)	100
Mount	Surface
Ordering number	0043260
Efficacy (Rated) (lm/w)	68.33
Average life (h) - L70/B50	30000
Technology	LED
Voltage (V)	220-240
Included lamp	Integrated LED
Compatible with bulbs of energy class:	A++ A+ A
Colour consistency (SDCM)	5 SDCM
Photobiological Risk Group	Group 0 (exempt)

DATA TABLE

General data

Certifications	CE
-----------------------	----

SylCircle

SYLCIRCLE 6W 410LM 4000K

0043260

Control gear type	Electronic
Dimmable	Non-dim / not dimmable (switched only)
EAN code	5410288432601
Environment	Internal
Fixture rating	Closed
General application	Residential & Consumer
Housing	Aluminium
Mount	Surface
Ordering number	0043260
Product name	SYLCIRCLE 6W 410LM 4000K
Average life (h) - L70/B50	30000
Technology	LED
Compatible with bulbs of energy class:	A++ A+ A
Product features	Ceiling / wall luminaire with integrated LED Perfect solution for hallways, kitchens or applicable zone 2 bathroom and wet areas thanks to its IP44 rating Even and uniform light distribution with a halo lighting effect on the wall surface 6W 410 lumens Supplied with LED driver (non-dimmable) IK03 PMMA diffuser Low maintenance with 30,000 hours LED life expectancy
What temperature Life is measured at (°C):	25

Optical data

Colour temperature (K)	4000
CRI (Ra)	80
Distribution type	Direct
Luminous flux (lm)	410
Light colour	Neutral white
LOR (%)	100
Colour consistency (SDCM)	5 SDCM
Photobiological Risk Group	Group 0 (exempt)

Physical data

Colour	White
Diffuser finish	Opal
Diffuser material	PMMA
Height (mm)	75
IK rating	IK03
IP rating	IP44
Lamp included	Integrated
Length (mm)	180

SylCircle

SYLCIRCLE 6W 410LM 4000K


0043260

Reflector finish	Diffuser
Weight (kg)	0.3
Width (mm)	180
Included lamp	Integrated LED

Electrical data

Drive current (mA)	150
Electrical protection	Class I
Glow wire test	650
Efficacy (Rated) (lm/w)	68.33
Total power consumption (W)	6
Voltage (V)	220-240

TECHNICAL DRAWINGS





SylCircle

SYLCIRCLE 6W 410LM 4000K


0043260


SYLVANIA 0043260


 This luminaire contains built in LED lamps.


 } LED


The lamps cannot be changed in the luminaire.





874/2012 

 This luminaire contains built in LED lamps.

The lamps cannot be changed in the luminaire.




 } LED

SYLVANIA 0043260  874/2012