

## SylCircle

SYLCIRCLE 12W 810LM 4000K

0043261



### Product features

- Ceiling / wall luminaire with integrated LED
- Perfect solution for hallways, kitchens or applicable zone 2 bathroom and wet areas thanks to its IP44 rating
- Even and uniform light distribution with a halo lighting effect on the wall surface
- 12W
- 810 lumens
- Supplied with LED driver (non-dimmable)
- IK03 PMMA diffuser
- Low maintenance with 30,000 hours LED life expectancy



## PRODUCT OVERVIEW

<b>Certifications</b>	CE
<b>Colour temperature (K)</b>	4000
<b>Colour</b>	White
<b>CRI (Ra)</b>	80
<b>Dimmable</b>	Non-dim / not dimmable (switched only)
<b>EAN code</b>	5410288432618
<b>Luminous flux (lm)</b>	810
<b>Housing</b>	Aluminium
<b>IK rating</b>	IK03
<b>IP rating</b>	IP44
<b>Light colour</b>	Neutral white
<b>LOR (%)</b>	100
<b>Mount</b>	Surface
<b>Ordering number</b>	0043261
<b>Efficacy (Rated) (lm/w)</b>	67.5
<b>Average life (h) - L70/B50</b>	30000
<b>Technology</b>	LED
<b>Voltage (V)</b>	220-240
<b>Included lamp</b>	Integrated LED
<b>Compatible with bulbs of energy class:</b>	A++ A+ A
<b>Colour consistency (SDCM)</b>	5 SDCM
<b>Photobiological Risk Group</b>	Group 0 (exempt)

## DATA TABLE

General data

<b>Certifications</b>	CE
-----------------------	----

## SylCircle

SYLCIRCLE 12W 810LM 4000K

0043261

<b>Control gear type</b>	Electronic
<b>Dimmable</b>	Non-dim / not dimmable (switched only)
<b>EAN code</b>	5410288432618
<b>Environment</b>	Internal
<b>Fixture rating</b>	Closed
<b>General application</b>	Residential & Consumer
<b>Housing</b>	Aluminium
<b>Mount</b>	Surface
<b>Ordering number</b>	0043261
<b>Product name</b>	SYLCIRCLE 12W 810LM 4000K
<b>Average life (h) - L70/B50</b>	30000
<b>Technology</b>	LED
<b>Compatible with bulbs of energy class:</b>	A++ A+ A
<b>Product features</b>	Ceiling / wall luminaire with integrated LED Perfect solution for hallways, kitchens or applicable zone 2 bathroom and wet areas thanks to its IP44 rating Even and uniform light distribution with a halo lighting effect on the wall surface 12W 810 lumens Supplied with LED driver (non-dimmable) IK03 PMMA diffuser Low maintenance with 30,000 hours LED life expectancy
<b>What temperature Life is measured at (°C):</b>	25

### Optical data

<b>Colour temperature (K)</b>	4000
<b>CRI (Ra)</b>	80
<b>Distribution type</b>	Direct
<b>Luminous flux (lm)</b>	810
<b>Light colour</b>	Neutral white
<b>LOR (%)</b>	100
<b>Colour consistency (SDCM)</b>	5 SDCM
<b>Photobiological Risk Group</b>	Group 0 (exempt)

### Physical data

<b>Colour</b>	White
<b>Diffuser finish</b>	Opal
<b>Diffuser material</b>	PMMA
<b>Height (mm)</b>	85
<b>IK rating</b>	IK03
<b>IP rating</b>	IP44
<b>Lamp included</b>	Integrated
<b>Length (mm)</b>	260

## SylCircle

SYLCIRCLE 12W 810LM 4000K


0043261

<b>Reflector finish</b>	Diffuser
<b>Weight (kg)</b>	0.4
<b>Width (mm)</b>	260
<b>Included lamp</b>	Integrated LED

### Electrical data

<b>Drive current (mA)</b>	150
<b>Electrical protection</b>	Class I
<b>Glow wire test</b>	650
<b>Efficacy (Rated) (lm/w)</b>	67.5
<b>Total power consumption (W)</b>	12
<b>Voltage (V)</b>	220-240

## TECHNICAL DRAWINGS




## SylCircle


SYLCIRCLE 12W 810LM 4000K

**0043261**


**SYLVANIA** 0043261





This luminaire contains built in LED lamps.




The lamps cannot be changed in the luminaire.




874/2012 




This luminaire contains built in LED lamps.



The lamps cannot be changed in the luminaire.



**SYLVANIA** 0043261  874/2012