

## SylCircle

SYLCIRCLE 24W 1600LM 4000K

0043263



### Range Features

- Ceiling / wall luminaire with integrated LED
- Perfect solution for hallways, kitchens or applicable zone 2 bathroom and wet areas thanks to its IP44 rating
- Even and uniform light distribution with a halo lighting effect on the wall surface
- 24W
- 1600 lumens
- Supplied with LED driver (non-dimmable)
- IK03 PMMA diffuser
- Low maintenance with 30,000 hours LED life expectancy

## PRODUCT OVERVIEW

<b>Certifications</b>	CE
<b>Colour temperature (K)</b>	4000
<b>Colour</b>	White
<b>CRI (Ra)</b>	80
<b>Dimmable</b>	Non-dim / not dimmable (switched only)
<b>EAN code</b>	5410288432632
<b>Luminous flux (lm)</b>	1600
<b>Housing</b>	Aluminium
<b>IK rating</b>	IK03
<b>IP rating</b>	IP44
<b>Light colour</b>	Neutral white
<b>LOR (%)</b>	100
<b>Mount</b>	Surface
<b>Ordering number</b>	0043263
<b>Efficacy (Rated) (lm/w)</b>	66.67
<b>Average life (h) - L70/B50</b>	30000
<b>Technology</b>	LED
<b>Voltage (V)</b>	220-240
<b>Included lamp</b>	Integrated LED
<b>Compatible with bulbs of energy class:</b>	A++ A+ A
<b>Colour consistency (SDCM)</b>	5 SDCM
<b>Photobiological Risk Group</b>	Group 0 (exempt)

## DATA TABLE

General data

<b>Certifications</b>	CE
<b>Control gear type</b>	Electronic

## SylCircle

SYLCIRCLE 24W 1600LM 4000K

0043263

<b>Dimmable</b>	Non-dim / not dimmable (switched only)
<b>EAN code</b>	5410288432632
<b>Environment</b>	Internal
<b>Fixture rating</b>	Closed
<b>General application</b>	Residential & Consumer
<b>Housing</b>	Aluminium
<b>Mount</b>	Surface
<b>Ordering number</b>	0043263
<b>Product name</b>	SYLCIRCLE 24W 1600LM 4000K
<b>Average life (h) - L70/B50</b>	30000
<b>Technology</b>	LED
<b>Compatible with bulbs of energy class:</b>	A++ A+ A
<b>Product features</b>	Ceiling / wall luminaire with integrated LED Perfect solution for hallways, kitchens or applicable zone 2 bathroom and wet areas thanks to its IP44 rating Even and uniform light distribution with a halo lighting effect on the wall surface 24W 1600 lumens Supplied with LED driver (non-dimmable) IK03 PMMA diffuser Low maintenance with 30,000 hours LED life expectancy
<b>What temperature Life is measured at (°C):</b>	25

### Optical data

<b>Colour temperature (K)</b>	4000
<b>CRI (Ra)</b>	80
<b>Distribution type</b>	Direct
<b>Luminous flux (lm)</b>	1600
<b>Light colour</b>	Neutral white
<b>LOR (%)</b>	100
<b>Colour consistency (SDCM)</b>	5 SDCM
<b>Photobiological Risk Group</b>	Group 0 (exempt)

### Physical data

<b>Colour</b>	White
<b>Diffuser finish</b>	Opal
<b>Diffuser material</b>	PMMA
<b>Height (mm)</b>	105
<b>IK rating</b>	IK03
<b>IP rating</b>	IP44
<b>Lamp included</b>	Integrated
<b>Length (mm)</b>	380
<b>Reflector finish</b>	Diffuser

## SylCircle

SYLCIRCLE 24W 1600LM 4000K

**0043263**


<b>Weight (kg)</b>	0.6
<b>Width (mm)</b>	380
<b>Included lamp</b>	Integrated LED

### Electrical data


<b>Drive current (mA)</b>	270
<b>Electrical protection</b>	Class I
<b>Glow wire test</b>	650
<b>Efficacy (Rated) (lm/w)</b>	66.67
<b>Total power consumption (W)</b>	24
<b>Voltage (V)</b>	220-240

**SYLVANIA** 0043263

---




This luminaire contains built in LED lamps.




}

L  
E  
D

The lamps cannot be changed in the luminaire.




874/2012



## SylCircle


SYLCIRCLE 24W 1600LM 4000K


**0043263**



This luminaire contains built in LED lamps.


The lamps cannot be changed in the luminaire.





A++  
A+  
A  
~~B~~  
~~C~~  
~~D~~  
~~E~~  
F

LED



**SYLVANIA** 0043263 874/2012