

ToLEDo Retro G80


ToLEDo RT G80 640lm E27 SL

0027173



Product features

- Perfect for decorative and general lighting applications and creates a warm ambiance similar to traditional lamps
- Same look, size and functionality as incandescent lamps
- Omni-directional light distribution
- First lamp of its type to achieve A++ rating - up to 128 lm/W
- Suitable for replacement of 50W incandescent lamps
- Gives same sparkling light effect as incandescent lamp
- 90% energy saving
- Dimensionally identical to incandescent lamps - fits all fixtures
- Environment friendly - no mercury and lower CO2 emissions
- Color temperature - 2700K Homelight
- Diameter - 80mm



PRODUCT OVERVIEW

Product code	0027173
Product name	ToLEDo RT G80 640lm E27 SL
Technology	LED
Watt (Rated) (W)	5.5
Type	ToLEDo Retro G80
Fixture rating	Open
General application	Hospitality, Residential & Consumer
Certifications	EUTIE103
ETIM Class	EC001959
E-number Finland	4740428
E-number Sweden	8290518
Luminous flux (lm)	640
Colour temperature (K)	2700
Light colour	Homelight
CRI (Ra)	80
Colour Variation Initial (SDCM)	6
Colour Consistency (SDCM)	6
Beam Angle (°)	300
Wattage (W)	5.5
Product Voltage (V)	230
Average life (Nominal) (h)	15000
Product EAN number	5410288271736

DATA TABLE

General data

Product code	0027173
Product name	ToLEDo RT G80 640lm E27 SL

ToLEDo Retro G80

ToLEDo RT G80 640lm E27 SL

0027173

Technology	LED
Watt (Rated) (W)	5.5
Type	ToLEDo Retro G80
Fixture rating	Open
General application	Hospitality, Residential & Consumer
Operating Temperature Range (°C)	25
Certifications	EUTIE103
ETIM Class	EC001959
E-number Finland	4740428
E-number Sweden	8290518

Optical data

Luminous flux (lm)	640
Luminous flux (Rated) (lm)	640
Colour temperature (K)	2700
Light colour	Homelight
CRI (Ra)	80
Colour Variation Initial (SDCM)	6
Colour Consistency (SDCM)	6
Beam Angle (°)	300
Beam angle (Rated) (°)	300
Lumen maintenance at end of nominal life (%)	70

Electrical data

Wattage (W)	5.5
Starting time (max) (s)	0.5
Warm-up time to 60% of full light (max) (s)	1
Product Voltage (V)	230
Lamp power factor	0.5
No. Of switching cycles before premature failures	50000
Lamp Energy Label (class)	A++
kWh per 1000 hours burning time	6
Nominal Frequency (Hz)	50Hz

Lifetime data

Average life (Nominal) (h)	15000
Average life (Rated) (h)	15000

Physical data

Nominal Product Length (mm)	116
------------------------------------	-----

ToLEDo Retro G80

ToLEDo RT G80 640lm E27 SL

0027173

Nominal Product Diameter (mm)	80
Weight (kg)	0.08

Packaging

Single packaging type	Carton
Product EAN number	5410288271736
Packaging single length (cm)	8.2
Packaging single width (cm)	8.2
Packaging single height (cm)	13.0
DUN14 (inner)	25410288271730
Units per inner package	6
Packaging inner length (cm)	14.7
Packaging inner width (cm)	17.4
Packaging inner height (cm)	25.8
DUN14 (outer)	15410288271733
Units per outer package	24
Packaging outer length (cm)	37.0
Packaging outer width (cm)	27.0
Packaging outer height (cm)	32.0

Safety data

Optimal operating condition (°C)	-10-45
Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Intended purpose	No
Dry applications use only	Yes
Suitable for household illumination	Yes

ToLEDo Retro G80
ToLEDo RT G80 640lm E27 SL
0027173

