


THIS DRAWING AND SPECIFICATIONS, HEREIN ARE THE CONFIDENTIAL PROPERTY OF SAMAR AND SHALL NOT BE REPRODUCED OR COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT WRITTEN PERMISSION.

REV.	DESCRIPTION	DRAWN / DATE	APPROVED / DATE
0	INITIAL RELEASE	FROS 07/07/2014	FROS 07/07/2014




200

135

DIMENSIONS ARE IN mm [INCH]		TOLERANCES ARE FRACTIONS DECIMALS ANGLES		MATERIAL		P/N 21-19084		DRAWN FROS		DATE 03/10/2014	
MOLD NO.		.x ± 0.20 [0.008]		FINISH		PROJECT NO.					
21-19084		.xx ± 0.12 [0.005]		COLOR		SCALE 1/1		SIZE A4		SHEET 1 OF 2	
				BREADBOARD PROJECT KIT				QC118			

THIS DRAWING AND SPECIFICATIONS, HEREIN ARE THE CONFIDENTIAL PROPERTY OF SAMAR AND SHALL NOT BE REPRODUCED OR COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT WRITTEN PERMISSION.

REV.	DESCRIPTION	DRAWN / DATE	APPROVED / DATE
0	INITIAL RELEASE	FROS 07/07/2014	FROS 07/07/2014



Number	Name	Q'ty	Number	Name	Q'ty
1	plastic box	1	18	LED light (random color)	1
2	breadboard (ZY-170, ZY-600, ZY-060)	5	19	LED light (random color)	1
3	jumper wire approximately 65 strips	1	20	LED light (random color)	1
4	5549 photoresistance	1	21	LED light (random color)	1
5	5V active buzzer	1	22	CD4069	1
6	speaker	1	23	CD4017	1
7	8050	1	24	LM386	1
8	8550	1	25	NE555	1
9	9013	1	26	CD4011	1
10	9012	1	27	CD4026	1
11	1N4148	1	28	LG5011ASR nixie tube	1
12	resistance 1/4W (100, 470, 1K, 4.7K, 10K, 20K, 47K, 100K, 200K, 510K, 1M)	each 10	29	monolithic capacitor (0.01u, 0.047u, 0.1u, 0.47u, 1uF)	each 10
13	battery 2032	1	30	microphone	1
14	LED light (red)	1	31	reed switch	1
15	LED light (green)	1	32	electrolytic capacitor (4.7u, 10u, 47u, 100u, 220uF)	each 1
16	LED light (yellow)	1	33	diode	1
17	LED light (random color)	1			

DIMENSIONS ARE IN mm [INCH]	TOLERANCES ARE FRACTIONS DECIMALS ANGLES	MATERIAL
MOLD NO.	.x ± 0.20 [0.008]	FINISH
21-19084	.xx ± 0.12 [0.005]	COLOR



BREADBOARD PROJECT KIT

P/N	21-19084	DRAWN	FROS	DATE	03/10/2014
PROJECT NO.					
SCALE	1/1	SIZE	A4	SHEET	2 OF 2
					QC118