


## P2662A

### Pylon Probe

Product Family: Pylon



#### Mechanical:

**Test Center (mil):** 50

**Test Center (mm):** 1.27

**Overall Length (mil):** 710

**Overall Length (mm):** 18.03

**Full Travel (mil):** 90

**Full Travel (mm):** 2.29

**Recommended Travel (mil):** 67

**Recommended Travel (mm):** 1.70

#### Thermal:

**Max Operating Temp (°C):** 85

**Min Operating Temp (°C):** -55

#### Electrical:

**Current Rating (Amps):** 3

**Average DC Resistance lower than (mOhm):** 30

#### Materials & Finishes:

**Plunger Material:** Heat-treated BeCu, Gold plated over hard Nickel

**Barrel Material:** Phosphor Bronze, Gold plated

**Ball Material:** Stainless Steel

#### Springs

Force Type - Preload in oz (g) - Rec. Travel in oz (g) -

Spring Material

Standard - 0.70 (2.00) - 1.70 (48.00) - BeCu, Silver plated

Alternate - 0.60 (17.00) - 2.50 (71.00) - BeCu, Silver plated

#### Body Type

Straight


Pylon Bend

## TIPS:


Tip Materials: BeCu, Gold plated

## Tips:


P2662-2V




P2662-1R



P2662-1Q



P2662-1C



## Related Products:

S2662A-3ED

