



3MP Flexible Intensifier® Technology Indoor Mini-Dome IP Camera

O3FDP9

2.8mm fixed lens, white housing



Features

- Flexible Intensifier® Technology fits any lighting application
- Supports up to 3MP @ 30fps
- Built-in standard PoE (IEEE 802.3af)
- Adaptive IR LEDs reduce IR saturation
- IR Range: 65' (depending on scene reflection)
- 3 axis lens mount
- True WDR (wide dynamic range) operation
- Micro SD card slot for edge recording (card not included)
- Conformant with ONVIF Profile S
- 5 year warranty



Camera Specifications

Image Sensor	Progressive scan 1/2.8" CMOS, 3MP
Maximum Resolution	2048 x 1536
Minimum Illumination	F1.4, Color: 0.1 lux; 0 lux (IR LED on)
Field of View (H)	108°
IR Range	65' (depending on scene reflection)
White Balance	AWT / AWB
Compensation	WDR
Day/Night	IR cut filter
Electronic Shutter Speed	1/30 - 1/100000 sec.
DNR	2D / 3D

Video Specifications

Main Resolution	2048x1536 / 1920x1080 / 1280x720 @ 30fps
Compression	H.264 (HP/MP/BP), MJPEG
Bitrate Control	VBR, CBR
Multiple Streaming	3 streams

Network Specifications

Protocols	IPv4, TCP, UDP, RTP, RTSP, HTTP, HTTPS, SMTP, FTP, DHCP, UPnP, DNS
DDNS Support	Speco DDNS (free of charge)
Security	User ID & Password protection, IP address filtering, digest authentication
User Access	Max. 8 simultaneous users. Actual number of users may vary depending on bandwidth

Client Specifications

Web Browser Support	Windows (Internet Explorer 8 and up)
PC Application	SecureGuard® VMS
Mobile	SecureGuard® Mobile (iPhone® and Android™)

Audio Specifications

Mono Input	N/A
Mono Input	N/A

External Terminal Specifications

Ethernet	10/100 Mbps
Power	DC jack
Storage	Micro SD slot

System Specifications

PoE	Standard (IEEE 802.3af)
Analytics	Motion detection, tampering
Alarm Triggers	Analytics
Alarm Events	FTP upload, email upload, micro SD card recording
Image Settings	Privacy mask

Operating & Unit Specifications

Power	PoE, 12VDC (power supply not included)
Power Consumption	5W
Operating Temperature	-4°F - 122°F
Operating Humidity	0% - 90% RH
Unit Dimensions	5.12" (Dia.) x 3" (H)
Unit Weight	10 oz.
Certifications	FCC, RoHS

Optional Accessories



POEINJ
12.95W
PoE Injector



PSW5
12VDC
Power Supply

Visit specotech.com for latest ONVIF® support. ONVIF is a trademark of Onvif, Inc. iPhone and iPad are trademarks of Apple Inc., registered in the U.S. and other countries. Android is a trademark of Google Inc. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 9/12/17



800-645-5516 • Fax: 631-957-9142 or 631-957-3880 • specotech.com

