

# 0 600 84A 171 – AdvancedHedgeCut 36

Material number	0 600 84A 171
EAN	3165140884099
1 battery pack 36V/2.0Ah lithium-ion battery	✓
Charger AL 3640 CV	✓



## Technical data

### Technical data

Battery type	Lithium-ion
Battery voltage	36 V
Works with battery capacity	2 Ah
Battery charge time	45 mins
Max. sqm per battery charge	300 sqm
Blade length	540 mm
Tooth opening	20 mm
No-load stroke rate	2.000 spm
Weight	3,6 kg

### Functions

“Anti-Blocking System”	✓
36 Volt	✓
Lithium-ion technology	✓

### Noise/vibration information

Sound pressure level	67 dB(A)
Sound power level	87 dB(A)
Uncertainty K	3 dB

## Sales information

---

### Positioning

- Cordless mobility and maximum power.

### User benefit

- Cordless freedom: no more having to untangle the cable or risking cutting through it.
- Powerful: combination of 540 mm blade length, 20 mm tooth opening and the electronic “Anti-Blocking System” ensures powerful cutting to get the job done.
- Always ready to use: 36 volt lithium-ion battery, compatible with other Bosch power tools. Completely charged in only 45 minutes (80% in 25 minutes).

### Highlights

- Syneon Chip – Intelligently controlled energy for every project
- Powerful 36 volt lithium-ion battery cuts up to 300 m<sup>2</sup> hedge per battery charge
- Innovative “Anti-Blocking System” for continuous cutting
- Saw function at the end of the bar enables cutting of branches up to 25 mm in diameter
- Ergonomic trigger position for comfortable hedge cutting in any working position
- Laser-cut, diamond ground precision blades for effortless cutting
- With additional blade protector for safe cutting along the edges of walls and the ground

