


TVIUTPPT – HD Video Transceiver with Pigtail (Balun)



Features:


- Send HD-TVI signal up to 656' (200M) over UTP cable.
- BNC male to screw terminal with 4" (10cm) mini coax cable for easy connection.
- Compact size allows mounting of multiple units behind multiplexers, Quads, DVRs, etc.
- Passive, No power required.
- Ideal for retrofits using existing UTP cable.
- Built in ESD, EFT (impulse noise), lightning (surge) and transient protection.
- Used in pairs (Sold individually).

Installation View:



The maximum functional distance is 656'. The distance may be affected by the quality of components (cable, camera resolution, DVR, etc.).

Item View:



Specifications:

ITEM NO.	TVIUTPPT
Video Input / Output Terminals	BNC MALE (75Ω · 1V p-p)
Video On put / Output Terminals	TERMINAL BLOCK
Bandwidth	50Hz ~ 60MHz (-3dB)
Transmission Distance	HD-TVI: 656' (200M)
ESD	30 KV(air) · 15 KV (contact) ; complaint IEC 61000-4-2
EFT (impulse noise)	40A(5/50ns) ; compliant IEC 61000-4-4
Lightning protection	2A (8/20μs) ; compliant IEC 61000-4-5
Surge Protection startup Time	< 1 nS
Environmental Specifications	Operation: 32°F to 131°F, Storage: -4°F to 185°F, Humidity: up to 95%
Dimension W x H x L	0.6" x 0.6" x 1.8", plus 4" mini coax cable
Weight	0.04 LBS



Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation.

Speco Technologies ☐ 200 New Highway ☐ Amityville ☐ NY ☐ 11701 ☐ www.specotech.com

Rev. 08/18/15