

FM10 Model

The Digimate series provides **low-cost, accurate food thermometers** for use in **catering and food processing environments**.

The FM10 pocket size digital thermometer is **ideal for checking core temperatures of food before serving**. Its large LCD and quick response time allow temperatures to be viewed quickly and easily.

The FM10 includes a pointed food shaft for easy insertion into food products and data hold for those hard to reach areas. Its handy pocket size and protective sheath allows users to carry around like a pen for quick checks when required.

General Specification

Water Resistant:	Yes
Auto Off:	Yes (after 35 minutes)
C/F Selection:	Yes
Data Hold:	Yes
Range:	-50°C to 150°C/-58°F to 300°F
Resolution:	0.1°C/°F
Accuracy:	1°C/2°F
Sampling time:	1.5 seconds
Battery:	1.5 Volt button (included)
Warranty:	3 months discretional

For other options, please contact us digitronsales@rototherm.co.uk or +44 (0)1656 740551



FM10 Model

Key Features and Benefits

- Water Resistant
- Quick response
- Auto Power Off
- Selectable Temperature Unit
- Large LCD

Main Applications

A **world leader** in digital thermometers, Rototherm has become the standard for accurate and reliable measurement across the following industries:



Food Service, Retail & Catering

Technical Certification

- Certificate of Conformity
- Factory Test Certificate
- Factory Calibration Certificate

Export Documentation


- Certificate of Origin
- EUR1
- ATR

Calibration and After-Sales Support

- Fully trained field service personnel
- Use of UKAS certified calibration equipment
- 5 day turnaround
- Fixed pricing
- Approved manufacturer parts
- Full post-service reports
- 12 month warranty



ISO9001:2008
FM11958



For more information, please contact our service team
digitronservice@rototherm.co.uk