


# PCH 6/ 4+4-G1L4-7,62 BK - 1717137

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


Header, nominal current: 41 A, rated voltage (III/2): 630 V, number of positions: 8, pitch: 7.62 mm, color: black, contact surface: Tin



## Why buy this product



## Key Commercial Data

Packing unit	25 STK
GTIN	 4 055626 514987
GTIN	4055626514987
Weight per Piece (excluding packing)	13.870 g
Custom tariff number	85366930
Country of origin	China

## Technical data

### Item properties

Number of positions	8
Pin layout	Linear pinning

### Dimensions for the product

Length [ l ]	28.2 mm
Width [ w ]	47.25 mm
Height (without solder pin)	16.4 mm
Solder pin [ P ]	2.6 mm

### Packaging information

Type of packaging	packed in cardboard
Pieces per package	25
Denomination packing units	Pcs.

## PCH 6/ 4+4-G1L4-7,62 BK - 1717137

### Technical data

#### Air clearances and creepage distances

Voltage	630 V
---------	-------

### Classifications

#### eCl@ss

eCl@ss 8.0	27440402
eCl@ss 9.0	27440402

#### ETIM

ETIM 5.0	EC002637
----------	----------