

100W


VT-40101 100W SMD FLOODLIGHTS COLORCODE:6500K BLACK BODY

Lumens 8500	Beam Angle 110	Dimensions 330x271x33mm
------------------------------	---------------------------------	--

White
SKU:5966




Instant Start: 0-100% in lt1s	IP Rating: IP65
Watts: 100	Dimmable: No
Lumens: 8500	Warranty (Years): 2
Beam Angle: 110	PF: >0.9
Unit Color: Black	CRI: >70
Body Type: Aluminium	Operation Temperature: -25 to +50°C
Long life: 20,000 Hours	Input Power: AC:220-240V,50Hz
LED Chip Type: SMD2835	Sensor Compatibility: Yes



Features

- ✓ Perfect replacement of Metal Halide Floodlight, High Pressure Sodium Floodlight & Halogen Floodlight
- ✓ Available in different color options of White , Day White, Warm White and RGB
- ✓ Fascia glass sealed with SILICONE RUBBER ensuring superior waterproof /airtight performance
- ✓ Premium Quality Aluminium Alloy body
- ✓ High Power LED chip
- ✓ Corrosion Resistant
- ✓ Built in driver - no external power supply required
- ✓ Excellent coverage for area and façade lighting
- ✓ Available from 10W up to 1000W
- ✓ Application - Building Façade, Sports Facilities, Industrial, Commercial Bill Boards & Hoardings, Parking Lots etc

Note:  Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	2.332
Length(Box)mm	36
Width(Box)mm	273
Height(Box)mm	335
Unit CBM	0.005093

Listing Details

EAN Code	3800157625593
Commodity Code	9405403990



Master Box Packaging

Master Box Qty (Pcs Per Carton)	5
Qty Per Pallet	240

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES