



8 Ch. Plug & Play Network Video Recorder and IP Camera Kit

ZIPL84D2

8 Channel NVR with 8 Channel Built-In PoE, 2TB
4 Full HD 2MP Outdoor IR Dome Cameras

ZIPL84B2

8 Channel NVR with 8 Channel Built-In PoE, 2TB
4 Full HD 2MP Outdoor IR Bullet Cameras

ZIPL88D2

8 Channel NVR with 8 Channel Built-In PoE, 2TB
8 Full HD 2MP Outdoor IR Dome Cameras

ZIPL88B2

8 Channel NVR with 8 Channel Built-In PoE, 2TB
8 Full HD 2MP Outdoor IR Bullet Cameras

ZIPL8BD2

8 Channel NVR with 8 Channel Built-In PoE, 2TB
4 Full HD 2MP Outdoor IR Dome Cameras,
4 Full HD 2MP Outdoor IR Bullet Cameras



Front panel



Rear panel

ZIPL8BD2 shown



Part Numbers for Kit Contents	
Recorder	N8NSL2TB
Cameras	O3VLD1K (dome)
	O3VLB3K (bullet)

Key Recorder Features

EZ Wizards - For ease of use and setup

Camera: quickly discovers and installs IP cameras

Setup: for setup of general settings

Network: network setup and port forwarding

Record: setup recording resolutions and recording type

Search: search for events from thumbnails

Copy: copy what you are playing onto a USB flash drive

- Built-In PoE IEEE 802.3af
- Video Out: 1 HDMI®, 1 VGA
- Plug & play feature with Speco's IP cameras
- Dual network ports for isolating IP camera network and remote network traffic
- **Free U.S.-Based DDNS Server Access**
- 5 year warranty¹

Additional Recorder Features

- Digital Deterrent® for triggering audio message via motion detection or sensor
- Full HD (1920 x 1080) recording and playback
- Switch between low and high quality stream during simultaneous Continuous + Motion or Continuous + Sensor recording modes for storage optimization
- Built-in S.M.A.R.T. Technology (Self-Monitoring, Analysis and Reporting Technology for HDD)
- Remote monitoring / recording / playback / configuration / software upgrades and PTZ control via internet
- Supports multiple PC based browsers such as Internet Explorer and Firefox
- Network accessible via SpecoTech Multi-Client Software, SecureGuard® VMS and Speco Player Mobile Viewer
- IR remote control and mouse included
- PC and MAC® compatible

Camera Features

- 2.8mm fixed lens
- Full HD 2MP @ 30fps
- Max 3MP @ 20fps
- Standard PoE
- True Day/Night operation
- IR LED operation
- IP67 compliant, weather resistant
- 5 year warranty

Camera Specifications	
Image Sensor	1/3" CMOS, 3MP
Max Resolution	2304x1296
Minimum Illumination	0 lux @F2.0 (IR on) / 0.37 lux @F2.0 (IR off)
S/N Ratio	50dB
Motion Detection	Yes
Day/Night	IR-cut filter
DNR	3D
IR Range	98' (depending on scene reflection)

Camera Operating & Unit Specifications	
Power Supply	PoE or 12VDC (power supply not included)
Power Consumption	4W
Operating Temperature	-20°F - 140°F
Camera Weight	Dome: 1 lb. / Bullet: 13 oz
Camera Dimensions	Dome: 4.33" (Dia.) x 3.19" (H) / Bullet: 2.75" (Dia.) x 6.49" (L)
NVR Weight	4 lbs.
NVR Dimensions	11.7" (W) x 2" (H) x 8.25" (D)

Optional Accessories



ERS1V
Vented Rack Shelf



IRRPTKIT
IR Repeater Kit

¹For supported IP camera models. ²Limited Warranty/Hard drives excluded. Check www.specotech.com for more details. iPhone is a trademark of Apple Inc., registered in the U.S. and other countries. Android is a trademark of Google Inc. The terms HDMI and HDMI High-Definition Multimedia Interface, and the HDMI Logo are trademarks or registered trademarks of HDMI Licensing LLC in the United States and other countries. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 1/31/18





Technical Specifications: Plug & Play Network Video Recorder

Model		NSL	
Video	Input	Max. IP Channels	8
		Resolution	Max. 1920 x 1080
	Output	HDMI®	1 HDMI (1280 x 720, 1920 x 1080)
		VGA	1 VGA (1280 x 720, 1920 x 1080)
Audio	Input	IP Camera (Network)	8
	Output	Local Output (RCA)	1
	Audio Codec	G.711	
Recording	Compression	H.264 (baseline, main and high profile)	
	Resolution	1080p	240fps
		720p	240fps
	Recording Mode	Continuous / Motion / Sensor / Schedule / Manual / Continuous + Motion / Continuous + Sensor	
	Pre-Recording	Max. 20 minutes	
	Post Recording	Max. 60 seconds	
Playback	Search	EZ Search, Date/Time, Event, Archive, Log	
	Multi-Decoding	1, 4, 8	
	Playback Speed	x0.25, x0.5, x2, x4, x8, x16, x32, x64	
Backup	Media	USB Drive, External HDD, Network	
	File Format	BMP, AVI, Proprietary Format	
	Large Backup	Yes (max. 24 hours)	
Storage	HDD	Capacity of 1 HDD	4TB
		Internal HDDs	1
	USB	Front	1
		Rear	1
User I/F	Input Method	IR, Mouse, Keyboard Controller	
Event	Sensor In	IP Camera (Network)	8
		Local Input (Terminal Block)	None
	Local Alarm Output (Terminal Block)	None	
	Motion Detection (From IP Camera)	Yes	
Network	LAN (IP Camera, Auto Connection)	8 (802.3af PoE)	
	WAN (IP Camera, Remote Access)	10/100Base-T	
	Protocols	TCP/IP, UDP, DHCP, HTTP, NTP, SMTP, RTP, RTSP	
	Max. Throughput	20Mbps	
Network Access	Mobile Viewer	iPad® / iPhone® / Android™	
	PC Web Viewer	Internet Explorer, Firefox	
	PC Client	SpecoTech Multi-Client Viewer and SecureGuard® VMS	
	MAC Client	Speco Client for MAC and SecureGuard® VMS	
	Remote Setup and Upgrade	Yes	
Features	Digital Deterrent®	Default + up to 8 audio files	
	Digital Zoom	Yes	
	DLS (Daylight Savings)	Yes	
	S.M.A.R.T	Yes	
	Internal Beep	Yes	
	Multi-Language	Yes	
	Dynamic DNS	Yes (free Speco DDNS)	
	Email Notification	Yes	
NTP (Network Time Protocol)	Yes		
Power Source	Power Supply Voltage	48VDC, 2.0A	
Allowable Operating Temperature		41° F - 104° F	
Allowable Storage Temperature		14° F - 122° F	
Weight	Unit Weight (Gross Weight)	4 lbs.	
Dimensions	Unit Dimensions (W x H x D)	11.7" (W) x 2" (H) x 8.25" (D)	

Please note that specifications and unit exterior design are subject to change without notification. Rev. 1/31/18



800-645-5516 • Fax: 631-957-9142 or 631-957-3880 • specotech.com

