

AT858D+(V3.0)

Intelligent hot air station

Economic

Applicable

- Production line
- Institutes
- Enterprises
- Education and Practice
- Maintenance
- Hobby



Package list	Standard Packing:
Main Unit: 1 PCS	Inner box : 26x18.5x15.5 (CM)
Hot Air Gun: 1 PCS	N.W.: 1.56KG
Gun Holder: 1pcs	G.W.: 1.75KG
AC Cord: 1 PCS	
Nozzle: 3 PCS	
Manual: 1pcs	

Nozzles



Heater



Features:

- Closed-loop and MCU zero crossing design for achieving fast heating-up, accurate and stable control.
- LED screen used to display working temperatures and working states make operations easy.
- Embedded sensor inside iron hand piece to obtain auto-sleep to save energy.
- Intelligence cooling system and deferred power-off function to extend hot air gun lifespan.
- Compact unit to save workbench space and eye-pleasing appearance.
- Intelligent malfunction detection and indications.
- Conserve a series frequently-used temperature & air flux. Digital control for air flow grades (A25-A99). Make normal temperature wind to cool the components.

Specification:

Voltage:	AC (100V/110V/120V 220V/230V/240V) 50/60Hz(Optional)
Power consumption:	700W
Temperature range:	100-500°C
Display mode:	LED display
Pump	fan type pump
Air flow gradation:	120L/min (MAX)
Noise:	<52dB(A)