

LED Floodlights



VT-200-B

HIGHLIGHTS :

WATTS



200

EQ. WATTS



100

LUMINOUS



16000

BEAM ANGLE



100

PRODUCT FEATURES

Item No	:	VT-200-B
SKU Code	:	419
Watts	:	200
Voltage	:	AC:220-240V,50Hz
Lumen(lm)	:	16000
Color Temperature	:	6400K
Beam Angle	:	100
PF	:	>0.9
LED Chip Type	:	SMD-Samsung Chip
CRI	:	>80
Certification	:	EMC,LVD,ROHS
IP Rating Protection Class	:	IP65
Body type	:	Die casting Aluminium
Dimmable	:	-
Life Time	:	30,000 Hours
Operation Temperature	:	-25 to +45°C
EAN code	:	3800157629164
Unit size	:	439x346x56mm
Packing details	:	2.00
Unit cbm	:	0.01420