

LED Bulb Series



VT-280

HIGHLIGHTS :

WATTS



10

EQ. WATTS



75

LUMINOUS



800

BEAM ANGLE



120

PRODUCT FEATURES

Item No	:	VT-280
SKU Code	:	135
Watts	:	10
EQ. Watts	:	75
Base / holder	:	E27
Voltage	:	AC:220-240V,50Hz
Lumen(lm)	:	800
Color Temperature	:	3000K
Beam Angle	:	120
Commercial type	:	R80
PF	:	>0.5
LED Chip Type	:	SMD-Samsung Chip
CRI	:	>80
Energy rating label	:	A+
Certification	:	EMC,LVD,ROHS
IP Rating Protection Class	:	IP20
Body type	:	Thermoplastic
Dimmable	:	No
Life Time	:	30,000 Hours
Operation Temperature	:	-25 to +45°c
EAN code	:	3800157627481
Unit size	:	ø80x114mm
Packing details	:	200.00
Unit cbm	:	0.00080