



Sample photo

Order symbol: AR884CHL
Product nbr: 8561087
Description: PC Enclosure
Remarks: Hinged opaque cover w/Plastic quick release latch

EAN: 6418074067302
El. number:
Finland:

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:			Accessories:		
mm:	203	203	102	ABP88	Painted Steel Back Panel
inch:	8.0	8.0	4.0	ALBP88	Aluminum Back Panel
				ADFP88	Dead Front Panel w/ screws
Materials:			ASP88		Aluminum Swing Panel
Material:	Polycarbonate		ASPK88		Swing Panel Kit incl. Panel
Base colour:	RAL 7035 -light grey		ASPHK8		Swing Panel Kit w/o Panel
Cover screws material:	Stainless steel		AMFL8		8" Mounting Flange Set
Cover colour:	RAL 7035 -light grey				
Gasket material:	Polyurethane				
Temperatures:			Rating:		
Temperature °C (short term):	-40 ... 140 °C		Ingress Protection (EN 60529): IP66/IP67		
Temperature °C (continuous):	-40 ... 80 °C		Electrical insulation: Totally insulated		
Temperature °F (short term):	-40 ... 284 °F		Halogen free (DIN/VDE 0472, Part 815): 0		
Temperature °F (continuous):	-40 ... 175 °F		UV resistance: UL 508		
			Flammability Rating: UL 508		
			Glow Wire Test (IEC 695-2-1) °C: 960		
			NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13		
Accessories:					
APBP88	PVC Back Panel				

