



Sample photo

**Order symbol:** AR10106CHSSL  
**Product nbr:** 8561112  
**Description:** PC Enclosure  
**Remarks:** Hinged opaque cover w/S.S.  
 Lockable latch

**EAN:** 6418074066770  
**El. number:**  
**Finland:**

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:	Length	Width	Height	Accessories:	
mm:	254	254	152	ABP1010	Painted Steel Back Panel
inch:	10.0	10.0	6.0	ALBP1010	Aluminum Back Panel
<b>Materials:</b>				ADFP1010	Dead Front Panel w/ screws
<b>Material:</b>	Polycarbonate			ASP1010	Aluminum Swing Panel
<b>Base colour:</b>	RAL 7035 -light grey			ASPK1010	Swing Panel Kit incl. Panel
<b>Cover screws material:</b>	Stainless steel			ASPHK10	Swing Panel Kit w/o Panel
<b>Cover colour:</b>	RAL 7035 -light grey			AMFL10	10" Mounting Flange Set
<b>Gasket material:</b>	Polyurethane			<b>Rating:</b>	
<b>Temperatures:</b>				Ingress Protection (EN 60529): IP66/IP67	
<b>Temperature °C (short term):</b>	-40 ... 140 °C			Electrical insulation: Totally insulated	
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			Halogen free (DIN/VDE 0472, Part 815): 0	
<b>Temperature °F (short term):</b>	-40 ... 284 °F			UV resistance: UL 508	
<b>Temperature °F (continuous):</b>	-40 ... 175 °F			Flammability Rating: UL 508	
<b>Accessories:</b>				Glow Wire Test (IEC 695-2-1) °C: 960	
APBP1010	PVC Back Panel			NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13	

