

Description

The CiT Classic Micro is a budget focussed Micro-ATX chassis aimed at business and home office solutions. The Classic Micro is equipped with 2 x USB 3.0 and 2 x USB 2.0 ports on the front I/O panel. The Classic Micro also includes a rear 80mm fan.

The Classic Micro is an ideal choice for anyone looking to build an office or home based PC on a budget.

Key Features

- **I/O Ports** - 2 x USB 3.0, 2 x USB 2.0 ports on front panel giving the user easy access.
- **Cooling** - Black chassis with 80mm rear cooling fan included.
- **Chassis** - Micro ATX Chassis with a simple design.
- **Side Panel** - Intel Approved TAC2.0 thermal chassis.
- **Interior** - Black coated interior.

Specifications

PSU Rail Output

(max.):

+3.3V: 26A

+5V: 27A

+12V: 22A

-12V: 0.5A

+5VSB: 2.0A

PSU Connectors

& Qty:

20 + 4pin ATX 1

Mainboard: 1

4pin +12V CPU: 1

SATA: 3

4pin Molex: 2

FDD: 1

:

Chassis Size

(Without the Front panel and Side Panel): (W) 173 x (H) 370 x (D) 365mm

Case Specifications

Form Factor: Micro ATX

Motherboard Support: Micro ATX, Mini ITX

PSU Support: Standard ATX

PSU Location: Top

Gaming Case: No

Water Cooling: Not Water Cooling Ready

Body Material: 0.5mm SPCC

Front Bezel Material: Plastic

Side Panel: Vented

Internal Cable

Management 21mm

Depth:

External Bays: 2 x 5.25" External
1 x 3.5" External

Internal Bays: 2 x 3.5" Internal
1 x 2.5" Internal

Drive Bay

Notes:

Expansion Slots: 4 x Full Size

Cooling Front: Space for 1 x 80mm

Cooling Top: None

Cooling Rear: Space For 1 x 80mm Fan (1 x 80mm Fan inc.)

Cooling Side: None

Cooling Bottom: None

2 x USB 3.0

IO Ports: 2 x USB 2.0

1 x HD Audio

1 x Microphone

GPU Max Length: 330mm

CPU Cooler Maximum Height: 160mm

Front Bezel Colour: Black

Body Colour: Black

System Cabinet Features: Supports Kensington Lock

PSU Included: Yes

General Specifications

Manufacturer: CIT CLASSIC MICRO

Part Number:

EAN Number: 5055492406125

Has Mains Plug: No

Colour: Black

What's In The Case:

Box: Screws

Unit (Product)

Dimensions (mm): 172mm x 414mm x 372mm (W x H x D)

Packaging

Dimensions (mm): 210mm x 447mm x 408mm (W x H x D)

Net Weight (KGs): 4.1 KGs

Gross Weight (KGs): 4.8 KGs