



Philips myGarden
Wall light

Raccoon
inox
LED

myGarden

17274/47/16



Always light when you come home

The Philips myGarden Raccoon wall light with brushed stainless steel look lights up outdoor areas powerfully. LED lights, synthetic materials and minimalist design give a contemporary feel, while a motion sensor keeps you extra safe.

Designed for your garden

- Motion sensor, for convenience and reassurance
- Easy to set up sensor
- IP44 - weather proof

Sustainable light solutions

- High quality LED light
- Philips offers a 5-year warranty on the LED module and driver
- Energy saving
- Warm white light
- Long operating life of up to 15 years

PHILIPS

Highlights

High quality LED light



The LED technology integrated into this Philips lamp is a unique solution developed by Philips. It turns on instantly, enables an optimal light output and brings out vivid colours in your home.

5-year warranty on LED system



On top of the standard 2-year warranty for this lamp, Philips offers a 5-year warranty on the LED system, meaning the LED module and the driver in this lamp.

Warm white light



Light can have different colour temperatures, indicated in units called Kelvin (K). Lamps with a low Kelvin value produce a warm, more cosy light, while those with a higher Kelvin value produce a cool, more energising light. This

Philips lamp offers warm white light for a cosy atmosphere.

Easy-to-set-up sensor



A simple set-up procedure makes it easy to select when and for how long the automatic sensor switches on the lamp(s).

Energy saving



This Philips energy-saving lamp conserves energy compared with traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

IP44 - weatherproof



This Philips outdoor light is especially designed for humid outdoor environments. It was tested


rigorously to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This outdoor light is designed with IP44: it is protected against splashing water. This product is most commonly used and ideal for general outdoor use.

Long operating life



A light source you can trust. The integrated LEDs used in this Philips LED lamp will last up to 15,000 hours (which equals 15 years on the basis of an average use of 3 hours/day with at least 13,000 on/off switching cycles) so you won't have to worry about maintenance or light bulb replacement whilst enjoying the perfect light ambience in your home.

Motion sensor



A motion sensor is included to welcome you when you return home or let you know when someone's coming.

Specifications

Design and finishing

- Material: synthetics, stainless steel
- Colour: inox

Extra feature/accessory incl.

- Motion sensor
- Fully weatherproof
- 5 year warranty on the LED module

Product dimensions and weight

- Height: 20.5 cm
- Length: 16.2 cm
- Width: 7.5 cm
- Net weight: 0.630 kg

Technical specifications

- Mains power: Range 220 V–240 V, 50-60 Hz
- Bulb technology: LED, Safety Extra Low Voltage
- Number of bulbs: 1
- Wattage bulb included: 3 W
- Light colour: warm white
- Total lumen output fixture: 270 lm

- Fixture dimmable: No
- LED
- Lifetime up to: 25,000 hrs
- IP code: IP44, protection against objects bigger than 1 mm, protection from splashed water
- Class of protection: II - double insulated
- Light source equivalent to traditional bulb of: 30 W

Service

- Warranty: 5 year(s)

Packaging dimensions and weight

- Height: 22.8 cm
- Length: 16.3 cm
- Width: 7.8 cm
- Weight: 0.703 kg

Miscellaneous

- Especially designed for: Garden and Patio
- Style: Contemporary
- Type: Wall light



Issue date 2018-01-24

Version: 2.0.1

12 NC: 9150 043 08801
EAN: 87 18291 47947 5

© 2018 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com