



Classic filament LED Lamps

CLA LEDBulb D 8-60W A60 E27 827 CL

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information		Lamp Current (Nom)	
Cap-Base	E27 [E27]		37 mA
Nominal Lifetime (Nom)	15000 h	Wattage Equivalent	60 W
Switching Cycle	20000X	Starting Time (Nom)	0.5 s
Technical Type	8-60W	Warm Up Time to 60% Light (Nom)	0.5 s
		Power Factor (Nom)	0.7
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)	55 °C
Luminous Flux (Nom)	806 lm		
Luminous Flux (Rated) (Nom)	806 lm	Controls and Dimming	
Color Designation	Warm White (WW)	Dimmable	Yes
Correlated Color Temperature (Nom)	2700 K		
Luminous Efficacy (Rated) (Nom)	107.47 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Finish	Clear
Color Rendering Index (Nom)	80		
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval and Application	
		Energy Efficiency Label (EEL)	A+
		Energy Consumption kWh/1000 h	8 kWh
Operating and Electrical			
Input Frequency	50 to 60 Hz		
Power (Rated) (Nom)	8 W		


Classic filament LED Lamps

Product Data

Full product code	871869670944300
Order product name	CLA LEDBulb D 8-60W A60 E27 827 CL
EAN/UPC - Product	8718696709443
Order code	929001331202
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	929001331202
Net Weight (Piece)	0.030 kg




Dimensional drawing



Bulb A60 230V7.5-60W 806lm 2700K D Clear

Product	D	C
CLA LEDBulb D 8-60W A60 E27 827 CL	60 mm	104 mm

Photometric data




LEDbulb 40W E27 827 CL A60 D

Classic filament LED Lamps

Lifetime



LEDbulb 40W E27 827 CL A60 D



LEDbulb 40W E27 827 CL A60 D

