

LED Bulb Series



VT-237

HIGHLIGHTS :

WATTS



8

EQ. WATTS



55

LUMINOUS



660

BEAM ANGLE



230

PRODUCT FEATURES

Item No	:	VT-237
SKU Code	:	145
Watts	:	8
EQ. Watts	:	55
Base / holder	:	E27
Voltage	:	AC:220-240V,50Hz
Lumen(lm)	:	660
Color Temperature	:	4000K
Beam Angle	:	230
Commercial type	:	T37
PF	:	>0.5
LED Chip Type	:	SMD-Samsung Chip
CRI	:	>80
Energy rating label	:	A+
Certification	:	EMC,LVD,ROHS
IP Rating Protection Class	:	IP20
Body type	:	Thermoplastic
Dimmable	:	No
Life Time	:	30,000 Hours
EAN code	:	3800157627580
Unit size	:	ø37x115mm
Packing details	:	200.00