

## LED Bulb Series



VT-250

### HIGHLIGHTS :

WATTS



6

EQ. WATTS



40

LUMINOUS



470

BEAM ANGLE



120

### PRODUCT FEATURES

Item No	:	VT-250
SKU Code	:	138
Watts	:	6
EQ. Watts	:	40
Base / holder	:	E14
Voltage	:	AC:220-240V,50Hz
Lumen(lm)	:	470
Color Temperature	:	3000K
Beam Angle	:	120
Commercial type	:	R50
PF	:	>0.5
LED Chip Type	:	SMD-Samsung Chip
CRI	:	>80
Energy rating label	:	A+
Certification	:	EMC,LVD,ROHS
IP Rating Protection Class	:	IP20
Body type	:	Thermoplastic
Dimmable	:	No
Life Time	:	30,000 Hours
Operation Temperature	:	-25 to +45°C
EAN code	:	3800157627511
Unit size	:	50x86mm
Packing details	:	200.00
Unit cbm	:	0.00020