

# LAD6K10F

## CONTACTOR MECH. LATCH CONTACT BLOCK IEC

Product availability : Stock - Normally stocked in distribution facility



### Main

Range of product	TeSys D control relay TeSys D
Range	TeSys
Product or component type	Mechanical latch block
Product compatibility	LC1D09...D38 LC1D40A...D65A TeSys D control relays LC1DT20...DT40 LC1DT60A...DT80A
[Uc] control circuit voltage	110/127 V AC 50/60 Hz 110/127 V DC

### Complementary

Mounting location	Front side
Tripping control	Manual Electrical
[Ui] rated insulation voltage	690 V - conforming to IEC 60947-5-1
Power required in VA	25 AC circuit
Power required in W	30 W for DC circuit
Mechanical durability	500000 cycles
Operating rate	1200 cyc/h
On-load factor	10 %
Product weight	0.15 lb(US) (0.07 kg)

### Environment

Product certifications	CSA UL
IP degree of protection	IP2x conforming to VDE 0106
Protective treatment	TH conforming to IEC 60068
Ambient air temperature for operation	-13...131 °F (-25...55 °C)
Ambient air temperature for storage	-40...176 °F (-40...80 °C)

## Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	00785901842385
Nbr. of units in pkg.	1
Package weight(Lbs)	0.22
Returnability	Y
Country of origin	FR

## Contractual warranty

Warranty period	18 months
-----------------	-----------