

Product data sheet

Characteristics

2510FG2

FHP Manual Starter - NEMA 1 - 2P - Toggle
Operated - No Indicator - 277VAC

Product availability : Stock - Normally stocked in distribution facility



Main

| | |
|---------------------------|----------------------------|
| Product or component type | Single Unit Manual Starter |
| Range of product | F |
| Thermal overload type | Melting alloy |

Complementary

| | |
|-----------------------|--|
| Line Rated Current | 16 A |
| Cable entry | 0.5" and 0.75" knock-outs (top and bottom) |
| Motor power hp | 1 hp at 115 V AC 1 hp at 277 V AC 0.75 hp at 115 V DC 0.75 hp at 230 V DC 2 hp at 230 V AC |
| System Voltage | 277 V AC 230 V DC |
| Poles description | 2P |
| Control type | Toggle switch |
| Phase | 1 phase |
| Local signalling | No indicator |
| Reset | Manual |
| Motor starter type | Non reversing |
| Electrical connection | Screw clamp terminals |
| AWG gauge | AWG 14...AWG 12 (copper) |
| Height | 4.25 in |
| Width | 2.44 in |
| Depth | 2.75 in |

Environment

| | |
|---------------------------|---|
| Product certifications | CSA LR25490 class 3211 05 CE UL listed file E42243 CCN NLRV |
| NEMA degree of protection | NEMA 1 plastic standard size |

Ordering and shipping details

| | |
|-----------------------|--------------------------|
| Category | 21101 - 2510,2511,2512 F |
| Discount Schedule | CP1 |
| GTIN | 00785901553953 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.7900000000000004 |
| Returnability | Y |
| Country of origin | MX |

Offer Sustainability

| | |
|------------------------|--|
| RoHS (date code: YYWW) | Will not be compliant Will not be compliant |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|