

# Product data sheet

## Characteristics

# 2510KO1

Manual Switch - Open - 2P - Toggle Operated -  
No Indicator - 600VAC

Product availability : Stock - Normally stocked in distribution facility



### Main

Product or component type	Single Unit Manual Switch
Range of product	K

### Complementary

Line Rated Current	30 A
Motor power hp	3 hp at 460 V AC 2 hp at 230 V AC 2 hp at 115 V AC 3 hp at 575 V AC 1 hp at 90 V DC 2 hp at 115 V DC 1.5 hp at 230 V DC
System Voltage	600 V AC 230 V DC
Poles description	2P
Control type	Toggle
Phase	1 phase
Local signalling	No indicator
Motor starter type	Non reversing
Electrical connection	Screw clamp terminals
AWG gauge	AWG 14...AWG 10 (copper)
Height	4.13 in
Width	1.69 in
Depth	2.34 in

### Environment

Product certifications	CE CSA LR25490 class 3211 05
------------------------	---------------------------------

UL recognized E42243 CCN NLRV2

---

NEMA degree of protection	Not rated (open device)
---------------------------	-------------------------

---

### Ordering and shipping details

---

Category	21102 - 2510,2511,2512 K
Discount Schedule	CP1
GTIN	00785901554554
Nbr. of units in pkg.	1
Package weight(Lbs)	0.35000000000000003
Returnability	Y
Country of origin	MX

---

### Offer Sustainability

---

RoHS (date code: YYWW)	Compliant - since 1545 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>

---

### Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---