

# Product data sheet

## Characteristics

# 2510MCO3

Manual Starter - Open Device - Buttons - 3P -

Size M1 - 600VAC

Product availability : Stock - Normally stocked in distribution facility



### Main

Product or component type	Manual Starter
Range of product	M
NEMA size	M-1

### Complementary

Control type	Push-button
Local signalling	No indicator
Motor power hp	7.5 hp at 200...230 V AC 3 phases 10 hp at 380...575 V AC 3 phases
System Voltage	600 V AC
Poles description	3P
Motor starter type	Non reversing
Electrical connection	Pressure wire clamp
Thermal overload type	Melting alloy
Number of thermal units required	3
AWG gauge	AWG 14...AWG 8 (copper)
Auxiliary contact composition	Without
Height	5.72 in
Width	3.5 in
Depth	4.03 in

### Environment

Product certifications	UL listed file E42243 CCN NLRV CSA LR60905 class 3211 05
NEMA degree of protection	Not rated (open device)

## Ordering and shipping details

Category	21103 - 2510,2511,2512 M,T
Discount Schedule	CP1
GTIN	00785901792208
Nbr. of units in pkg.	1
Package weight(Lbs)	2.2000000000000002
Returnability	Y
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

## Contractual warranty

Warranty period	18 months
-----------------	-----------