



TRIAX

connecting the future



LTE HG 10 T - Ch. 21...60 - 15dBi Gain - LTE 800 Protected Antenna / Aerial

Article number: 108175

Product description:

- LTE Protected
- Tool free assembly - Quick lock dipole and reflector
- Strong, rugged construction
- F-Connector dipole housing
- Excellent F/B ratio and performance across the whole UHF band

Specifications

ORDER INFORMATION	
EAN Number	5702661081750
CHARACTERISTICS	
Type.	HG 10 T
FREQUENCY	
Band	B IV/V UHF
Channels	21...60
Frequency range UHF	470...790 MHz
LTE protection	800

GAIN	
Gain	13...15 dBi
LOSS	
Rejection @ 821 MHz (LTE D6)	<2.14dBi dB
ELECTRICAL	
Front to back ratio - horisontal	24 dB
Impedance	75 Ω
CONNECTORS	
Connector Type	F-female
MECHANICAL	
Elements	52
Windload	96 N
Beamwidth horisontal	32 °
Beamwidth vertical	35 °
Bracketry	Centre Support
Construction type	Quick Lock Reflectors and Dipole
Main material	Aluminium
Individual brown box	Yes
Product Length	1220 mm
Product Width	610 mm
Packing QTY	1
Net Weight	2,250 kg
Total Weight	2,250 kg